## HG RACK 2U PRO (SX 3080)

PEM Rack 19 inch Hydrogen generator

**Main Applications** 

- Carrier gas for GC and GC-MS
- GC-FID / GC-NPD / GC-FPD
- TH/

**Main Advantages** 

- Quick installation
- Easy use
- ✔ Hydrogen flow rate up to 600 cc/min
- ✔ Pressure up to 16 bar (232 psi)
- ✔ Hydrogen purity: 99.99999%
- RS 485 and USB as standard
- LAN optional
- Dryer with no maintenance
- ✔ Reduced foot print: 19 inch rack 2U
- High pressure GLS electronically controlled (patented)

The HydroGen series **HG RACK 19" 2U PRO** is able to generate up to 600cc/min Hydrogen with purity better than 99.99999% and pressure up to 16 bar (232 PSI).

The **HG RACK 19 inch 2U PRO** includes an electrolytic cell with polymeric membrane (PEM) using distilled water. The two-column PSA drying system with automatic regeneration ensures the maximum grade of hydrogen purity, and is completely maintenance-free.

The **HG RACK 19 inch 2U PRO** is the ideal Hydrogen for all GC-FID detectors. The on-board CPU constantly controls the operating parameters to guarantee full safety.

Up to 20 units can be connected in parallel mode using an external control box. The touch-screen LCD interface provides simple and user-friendly management of all functions on the unit.









100	160	250	350	600
PEM technology				
PSA (Pressure Swing Adsorption)				
>99.99999% *1				
12 bars (174 psi) / 16 bars (232 psi) (optional)				
100	160	250	350	600
	Standard 19	inch 2U RACK (	48 cm deep)	
16.5 kg				
Standard				
Optional				
Ready on board				
Standard				
Deionized, ASTM II, <0.1uS				
-0.2 bars (1.4 psi), 0.5 bar (7.25 psi)				
		0.3 l		
	IEC 320-C14			
100-240 Vac (±10%) 4763 Hz				
350W		500W		
4A (250VAC – T)				
	1/8" compression fitting			
	Quick release push-in fitting			
	100	PSA (Pre  12 bars (174 ps  100 160  Standard 19  Deior -0.2 bars (  100-24  35	PEM technology PSA (Pressure Swing Ads >99.999999% *1  12 bars (174 psi) / 16 bars (232  100  160  250  Standard 19 inch 2U RACK ( 16.5 kg  Standard  Optional  Ready on board Standard  Deionized, ASTM II, < -0.2 bars (1.4 psi), 0.5 bar 0.3 l  IEC 320-C14  100-240 Vac (±10%) 47 350W 4A (250VAC - T)  1/8" compression fi	PEM technology PSA (Pressure Swing Adsorption) >99.99999% *1  12 bars (174 psi) / 16 bars (232 psi) (optional)  100  160  250  350  Standard 19 inch 2U RACK (48 cm deep)  16.5 kg  Standard  Optional  Ready on board  Standard  Deionized, ASTM II, <0.1uS -0.2 bars (1.4 psi), 0.5 bar (7.25 psi)  0.3 l  IEC 320-C14  100-240 Vac (±10%) 4763 Hz 350W  4A (250VAC – T)  1/8" compression fitting

<sup>\*1</sup> Referred to O<sub>2</sub> - DewPoint < -75°C (<-103°F), Atmospheric Dew Point (ADP)

Ordering codes	
Gas Generators	
6920.16.010	HG 2U PRO 100
6920.16.016	HG 2U PRO 160
6920.16.025	HG 2U PRO 250
6920.16.035	HG 2U PRO 350
6920.16.060	HG 2U PRO 600
Consumable	
6930.00.091	Deionizer water filter

